

Contact/Phone:

# Project: Fixture Type: Location:

# 4" MINIATURE UNIVERSAL IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

#### PRODUCT DESCRIPTION

IC Air-Loc® New Construction Housing • Air-Loc rated with all IC-rated 4" trims and complies with the Washington State and IECC Energy Codes • Energy efficient, sealed inner housing • Double wall housing construction • Air-Loc housing stops infiltration and extiltration of air, reducing heating and cooling costs • Can be completely covered with insulation.

#### PRODUCT SPECIFICATIONS

**Lamp** Lamp ratings based on trim selected – see reverse.

**Socket** Detachable medium base porcelain with nickel-plated copper screw shell.

**Trims** Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP

- Product thermally protected against improper use of lamps
- Union made UL and cUL Listed Trim No. 11, 12, 4101, 4102 and 4181 are wet location approved for covered ceiling applications
- Trims 14, 17 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

**Testing** All reports are based on published industry procedures; field performance may differ from laboratory performance.

Specifications subject to change without notice.

#### **INSTALLATION**

Real Nail 3 Bar Hangers Telescoping Real Nail® 3 system covered under US Patent D552,969 permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

**Junction Box** Pre-wired junction box provided with (6) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, UL and cUL listed for through-branch wiring, maximum 6 No. 12 AWG 90° C branch circuit conductors (3 in, 3 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

**Mounting Frame** 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.


**Housing** Air-Loc IC housing, .032" aluminum • Inner housing is vertically adjustable to accommodate up to a 2" ceiling thickness.


#### **PRODUCT CODES**

Catalog Number		Voltage	Lamp Rating (max.)	
IC1P	4" Incandescent New Construction	120V	K19/R14/R16/R20/PAR16/PAR20/GU10 Base Lamps	
	Housing		(see reverse for max. trim rating)	

Housing and trim can be ordered together or separate, but will always ship separately.

#### **DIMENSIONS**





#### **ACCESSORIES**

Catalog No.	Description
GU10WHIP	GU10 Socket Whip

To order, specify catalog number

# 4" MINIATURE UNIVERSAL IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS IC1P

### **ROUND TRIMS/LAMPS**

		Cat. No.	Description	Max. Lamp Rating
AIR-LOC		13 WH	4" Pinhole with Integral Shield - White	50W PAR20/R20, 50W PAR20, 40W K19
AIR-LOC		14 BBRZ ◆	4" Downlight Baffle Trim - Black Baffle, Bronze Trim Ring	50W PAR20/ R20
		14 BBL ◆	4" Downlight Baffle Trim - Black Baffle, Black Trim Ring	
		14 BSC ◆	4" Downlight Baffle Trim - Black Baffle, Satin Chrome Trim Ring	
		14 BWH ◆	4" Downlight Baffle Trim - Black Baffle, White Trim Ring	
		14 WWH ◆	4" Downlight Baffle Trim - White Baffle, White Trim Ring	
		17 BWH ◆	Aff Door Edu Coo. Time Deals Coo. White Time Dis-	COMPINION MON
AIR-LOC		17 GWH ◆	4" Downlight Cone Trim - Black Cone, White Trim Ring	50W PAR20 /R20
			4" Downlight Cone Trim - Clear Alzak® Cone, White Trim Ring	
		17 HZWH ◆ 17 PTSC ◆	4" Downlight Cone Trim - Haze Cone, White Trim Ring	
		17 PISC♥  17 WHZBRZ ♦	4" Downlight Cone Trim - Pewter Cone, Satin Chrome Trim Ring	
		17 WHZWH ◆	4" Downlight Cone Trim - Wheat Haze Cone, Bronze Trim Ring	
		17 WHZWH ◆	4" Downlight Cone Trim - Wheat Haze Cone, White Trim Ring 4" Downlight Cone Trim - White Cone, White Trim Ring	
		17 WW⊓ <b>▼</b>	4 Downingin Cone mini - while cone, while mini king	
AIR-LOC	- <b>-</b>	10 BRZ	4" Flush Gimbal Ring Trim - Bronze	50W PAR20
		10 BL	4" Flush Gimbal Ring Trim - Black	
		10 SC	4" Flush Gimbal Ring Trim - Satin Chrome	
		10 WH	4" Flush Gimbal Ring Trim - White	
AIR-LOC		18 WH	4" Adjustable Mini Eyeball Trim - White	60W PAR16
		12 WWH ◆	4" Frosted Lens with Clear Center Trim - White, White Trim Ring	50W PAR20/R20 with 1" socket extender #1599
AIR-LOC		12 WBRZ ◆	4" Frosted Lens with Clear Center Trim - Perimeter Frosted Lens, Bronze Trim Ring	
		12 WSC ◆	4" Frosted Lens with Clear Center Trim - Perimeter Frosted Lens, Satin Chrome Trim Ring	
			,	
AIR-LOC		16 WH	4" Adjustable Scoop Trim - White	40W R14, 40W R16 (Intermediate screw base)
AIR-LOC		4101 WH ◆	4" Decorative Beveled Dome Lens Trim - White	50W PAR20 /R20
AIR-LOC		4181 CLEAR ◆	4" Decorative Frosted Glass Trim - Perimeter Frosted Clear Glass	COMPANDO 7000
AIRGIOG		+101 CLEAR ♥	4 Decoraine Francisco diazz IIIIII - Ferinieriei Frazieo Ciedi diazz	50W PAR20 /R20

# 4" MINIATURE UNIVERSAL IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

## IC1P

### FOR GU10 BASE LAMPS (MUST USE GU10WHIP)

ARLOC (

 Cat. No.
 Description

 440 BRZ
 4" Adjustable Flush Gimbal Ring Trim - Bronze

 440 SC
 4" Adjustable Flush Gimbal Ring Trim - Satin Chrome

 440 BL
 4" Adjustable Flush Gimbal Ring Trim - Block

 440 WH
 4" Adjustable Flush Gimbal Ring Trim - White

Max. Lamp Rating
50W MR16/PAR16/ES16 (120V GU10 Base)

AIR-LOC



445 WH

4" Adjustable Slot Aperture Trim - White

50W MR16/ES16 (120V GU10 Base)

AIR-LOC



446 WH

4" Wall Wash Adjustbale Scoop Trim - White

50W MR16/ES16 (120V GU10 Base)

Air-Loc



)

 10 BRZ
 4" Flush Gimbal Ring Trim - Bronze

 10 BL
 4" Flush Gimbal Ring Trim - Black

 10 SC
 4" Flush Gimbal Ring Trim - Satin Chrome

 10 WH
 4" Flush Gimbal Ring Trim - White

50W PAR20 / 75W ES20 (120V GU10 Base)



GU10WHIP

Medium Base to GU10 Adapter - GU10 Socket Whip

#### **SQUARE TRIMS/LAMPS**

Cat. No.

Description

4" Square Downlight Trim - Black, White Trim Ring

175Q HZWH ◆◆

4" Square Downlight Trim - Haze, White Trim Ring

175Q WHZWH ◆◆

4" Square Downlight Trim - Wheat Haze, White Trim Ring

175Q WWH ◆◆

4" Square Downlight Trim - White, White Trim Ring

Max. Lamp Rating 50W PAR20, 50W R20



13SQ WH

4" Square Pinhole Trim - White

50W PAR20, 30W R20



12SQ WWH ◆

4" Sqaure Frosted Lens with Clear Center Trim - White, White Trim Ring

50W PAR20/R20



440SQ BL 440SQ WH 4" Square Flush Gimbal Trim - Black 4" Square Flush Gimbal Trim - White 50W MR16/120V GU10 Base (Requires GU10WHIP) 35° Vertical Adjustment

Trim Size: 5" O.D.

Alzak is a registered trademark of Alcoa Corp.

Note: In Canada when insulation is present, Type IC fixtures must be used.

AIR-LOO JUNO IC housings meet IECC Energy Code requirements per ASTM E283.

Air-Loc® roted trims are pre-gasketed for minimum air leakage with IC housings.

- UL Listed for use in wet location.
- ◆◆ UL Listed for use in wet location with outdoor rated lamp.

Light Commercial & Residential