

Project:	
Fixture Type:	
Location:	
Contact/Phone:	

# **6" ECONOMY UNIVERSAL** IC REMODEL HOUSING

INCANDESCENT LAMPS

IC22R

## **PRODUCT DESCRIPTION**

IC Air-Loc® Remodel Housing • Energy efficient, sealed housing • IC Remodel Housing for remodel application where back side of ceiling is not accessible • Installs through an opening in the ceiling from below • Secured in place by factory installed remodel springs • Can be completely covered with insulation • When used with Air-Loc Gasket, stops infiltration and exfiltration of air, reducing heating and cooling costs • Trims shown with Air-Loc symbol ARLOC do not require gasket.

## **PRODUCT SPECIFICATIONS**

Lamp Lamp ratings based on trim selected-see page 2.

**Socket** Medium base porcelain with nickel-plated copper screw shell • Drop socket with spring to accommodate certain trim installation.

**Trims** Trim selection shown on page 2.

Labels UL listed for through-branch wiring, damp locations and IP

- Product thermally protected against improper use of lamps
- Union made UL Listed/CSA certified Trims 239, 241 and 242 are wet location approved for covered ceiling applications • Trims 28, 29 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.


Specifications subject to change without notice.


## **INSTALLATION**

Junction Box Pre-wired junction box, UL listed/CSA certified for through-branch wiring maximum 4 No. 12 AWG 90° C branch circuit conductors (2 in, 2 out) • Junction box provided with removable access plate, (5) ½" knockouts, (4) Non-metallic sheathed cable connectors and ground wire • Knockouts equipped with pryout slots.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Double stack adjustable feature enables remodel spring to accommodate up to  $1\frac{3}{4}$ " ceiling thickness.

## **DIMENSIONS**





6 3/4" CEILING CUTOUT

Accessories		
Catalog Number	Description	
ALG6R	Air-Loc Gasket	

To order, specify catalog number.

#### **PRODUCT CODES**

Cat	alog Number	Input Voltage	Lamp Rating
IC2	2R 6" Incandescent Remodel IC Housing	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See page 2 for max. trim rating)

Housing and trim can be ordered together or separate, but will always ship separately.

# **6" ECONOMY UNIVERSAL** IC REMODEL HOUSING

INCANDESCENT LAMPS

IC22R

#### TRIMS/LAMPS

	Catalog Number	Description	Max. Lamp Rating			Catalog Number	Description	Max. Lamp Rating	
**	24 BWH 24 BSC 24 BABZ 24 BBL 24 WWH	Black Baffle, White Trim Ring Black Baffle, Satin Chrome Trim Ring Black Baffle, Classic Aged Bronze Trim Ring Black Baffle, Black Trim Ring White Baffle, White Trim Ring	50W PAR30, 75W PAR30L, 65W BR30	AIR-LOC		239 WH ◆ 241 WH ◆ 241 PW ◆	Frosted Lens, White  Drop Opol w/Reflector, White Drop Opol w/Reflector, Plastic White	40W A19	
**	25 BWH 25 BSC 25 BABZ 25 BBL	Black Baffle, White Trim Ring Black Baffle, Satin Chrome Trim Ring Black Baffle, Classic Aged Bronze Trim Ring Black Baffle, Black Trim Ring	50W PAR30, 65W BR30	AR-LOC (		242 WH ◆ 242 SC ◆ 242 ABZ ◆	Frosted Lens w/Clear Center, White Safin Chrome Classic Aged Bronze	45W PAR38	
ARLOC ARLOC	25 WWH 28 BWH ◆◆ 28 WWH ◆◆	White Baffle, White Trim Ring Black Baffle, White Trim Ring White Baffle, White Trim Ring	60W A19, 65W BR30, 75W PAR30/30L,	(		9324 SC 9702	Luminous Frosted Disc, Satin Chrome  Luminous Collar (Frosted)	50W PAR30, 65W BR30 50W PAR30,	
Air-Loc	29 CWH ◆◆ 29 WWH ◆◆	Clear Cone, White Trim Ring White Cone, White Trim Ring	90W PAR38, 90W BR40 60W A19, 65W BR30, 75W PAR30/30L,	(				65W BR30, 75W PAR30L	
	27 CWH	Clear Alzak® Cone, White Trim Ring	90W PAR38, 90W BR40 50W PAR30,	C		9024 WWH	Octagonal, White, White Trim Ring	50W PAR30, 65W BR30,	
** AIRLOG	27 GWH 27 BWH 27 PTSC 27 WWH 27 HZWH 27 WHZWH 27 WHZABZ	Gold Cone, White Trim Ring Black Cone, White Trim Ring Pewter Cone, Soutin Chrome Trim Ring White Cone, White Trim Ring Haze Cone, White Trim Ring Wheat Haze Cone, White Trim Ring Wheat Haze Cone, Classic Aged Bronze Trim Ring	75W PAR3OL, 65W BR3O	Š		9524 SC	Metal Band, Satin Chrome	65W BR3O, 50W PAR3O, 75W PAR3OL	
**	244S BWH 244S WWH	Black Baffle, White Trim Ring White Baffle, White Trim Ring	75W PAR3OL, 60W PAR3O, 65W BR3O						
## (Incloded)	247S CWH 247S GWH 247S BWH 247S HZWH 247S WHZWH	Clear Alzak® Cone, White Trim Ring Gold Alzak® Cone, White Trim Ring Black Alzak® Cone, White Trim Ring Haze Cone, White Trim Ring Wheat Haze Cone, White Trim Ring	75W PAR3OL, 65W BR3O, 75W PAR3O						
	250 WH 250 SC 250 ABZ	Open Frame, White Open Frame, Satin Chrome Open Frame, Classic Aged Bronze	65W BR30						
	252 WH	Regressed Open Frame, White	75W R/BR30						
	231 CWH 231 GWH 231 WWH	Clear Alzak®, White Trim Ring Gold Alzak®, White Trim Ring White, White Trim Ring	60W A19						
	226 BWH 226 WWH	Cylinder Spotlight, Black Baffle, White Trim Ring Cylinder Spotlight, White Baffle, White Trim Ring	60W PAR16		Trim Sizo	. 75/″ ∩ D. Joy	cont Cat. Nos. 228, 220	241 0024	
	228 WH	Regressed Eyeball, White	50W PAR20/R20		- 8" O.D.	Trim Size: 75%" O.D. (except Cat. Nos. 228, 229, 241, 9024, -8" O.D., Cat. No. 9702 - 73/4" O.D.).  Alzak is a registered trademark of Alcoa Corp.  Note: In Canada when insulation is present, Type IC fixtures must be used.  JUNO IC housings meet IECC Energy Code requirements per ASTM E283.  Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.			
	229 WH 229 SC 229 ABZ 229 BL	Regressed Eyeball, White Regressed Eyeball, Satin Chrome Regressed Eyeball, Classic Aged Bronze Regressed Eyeball, Block	75W PAR3OL, 65W BR3O	Air-Loc	Note: In 0 must be u				
	248 WWH	Regressed Eyeball, White Baffle, White Trim Ring	50W PAR20/R20		ASTM E2				
	249 BWH 249 WWH	Regressed Eyeball, Black Baffle, White Trim Ring Regressed Eyeball, White Baffle, White Trim Ring	75W PAR3OL, 65W BR3O						
**	264 BWH 264 WWH	Adjustable, Black Baffle, White Trim Ring Adjustable, White Baffle, White Trim Ring	50W PAR30			◆ UL Listed for use in wet location.			
**	267 CWH 267 GWH 267 BWH 267 HZWH 267 WHZWH	Clear Alzak® Cone, White Trim Ring Gold Alzak® Cone, White Trim Ring Black Alzak® Cone, Whit Trim Ring Haze Cone, White Trim Ring Wheat Haze Cone, White Trim Ring	50W PAR30		** NOT 264,	◆◆ UL Listed for use in wet location with outdoor rated lamp.  ** NOTE: TR6 Trim Ring compatible with 24, 25, 27, 244S, 247S, 264, 267 trims.  Housing and trim can be ordered together or separate, but will always ship separately.			