



Description

IC rated, energy efficient Air-Loc® sealed housing • Can be completely covered with insulation • Air-Loc installation stops infiltration and exfiltration of air, reducing heating and cooling costs

Listings

UL Listed, C-UL/CSA certified for through-branch wiring, damp and wet locations • Wet location listed with the 239, 241 and 242 trims • Trims 28 and 29 are wet location approved when used with PAR30/PAR38 outdoor rated lamps • Washington State IECC and MEC energy codes as tested per ASTM-E283 • Conforms with City of Chicago IP requirements

Features

- 6" Housing
- Adjustable socket plate and detachable socket with snap-in springs to accommodate various lamp and trim combinations
- Socket plate is secured at two points for consistent, straight lamp positioning
- Medium base porcelain socket with nickel-plated copper screw shell
- Shipped with socket cap to protect against paint overspray
- Housing is vertically adjustable to accommodate up to a 1" ceiling thickness
- Real Nail® 3 bar hangers: telescoping system with pre-installed removable nail for easy repositioning of housing in joist construction • Integral T-bar mounting feature for secure installation in suspended ceilings
 - Patented breakaway bars for tight joist spacing
 - Bar hangers may be re-positioned 90°
 - Curved foot facilitates alignment with joist bottom
 - Quick-Loc slot and oversized set screw lock fixture in position
- Housing is fully assembled for ease of installation
- Pre-wired junction box with (5) 1/2" and (1) 3/4" knockouts with pryout slots, (4) non-metallic sheathed cable connectors, and ground wire
- Shadow-free, knife-edge trim design blends smoothly into the ceiling and allows architectural continuity with Aculux® trims
- UL Listed, C-UL/CSA certified for through-branch wiring, maximum (8) #12 AWG branch circuit conductors (4 in, 4 out)
- Thermally protected against improper use of lamps
- Lamp wattage ratings and apertures based on trim selection. Trim selection follows IC22 Series

Ordering Information

Catalog No.	Description
IC22	6" Incandescent housing
IC22W	IC22 with push-in electrical connectors for fast, secure installation
IC22S	IC22 with smaller footprint bar hanger (Real Nail® 2)

Accessories

Catalog No.	Description
ALG6	Air-Loc® Energy Conserving Gasket for 6" Air-Loc IC housings

Dimensions

