

roject:
ixture Type:
ocation:
Contact/Phone:

6" ECONOMY UNIVERSAL IC HOUSING

INCANDESCENT LAMPS

IC23 SERIES

PRODUCT DESCRIPTION

IC Air-Loc® Housing • Energy efficient, sealed housing • Can be completely covered with insulation • When used with Air-Loc Gasket accessory or pre-installed gasket on mounting frame, stops infiltration and exfiltration of air, reducing heating and cooling costs • Trims shown with Air-Loc symbol Air-Loc do not require a gasket.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected - see page 2.

Socket Medium base porcelain with nickel-plated copper screw shell

• Floating socket with spring attaches to trim for installation.

Trims Trim selection shown on page 2.

Labels UL listed for through-branch wiring, damp locations and IP Product thermally protected against improper use of lamps
 UL Listed/ CSA certified • Trims 239 and 241 are wet location approved for covered ceiling applications • Trims 28, 29 are wet location approved for covered ceilings, must be used with outdoor rated lamps.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance. Specifications subject to change without notice.

INSTALLATION

Real Nail® 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid - no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position


- Bar hanger foot contoured to align to bottom of construction joist
- Alternate mounting holes included.


Junction Box Pre-wired junction box provided with $(5) \frac{1}{2}$ and $(1) \frac{3}{4}$ knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots • W options are supplied with push-in electrical connectors for fast installation.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation • Sight lines embossed on mounting frame to allow for easy viewing when aligning fixtures Pre-installed Air-Loc gasket for G options.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Housing is vertically adjustable to accommodate up to a 1" ceiling thickness.

DIMENSIONS





67/8" CEILING CUTOUT

Accessories

Catalog Number	Description	
ALG6	Air-Loc Gasket	

To order, specify catalog number

PRODUCT CODES

Catalog Numl	ber	Input Voltage	Lamp Rating
IC23	6" Incandescent No Plate New Construction IC Housing	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See page 2 for max. trim rating)
IC23 G	6" Incandescent No Plate New Construction IC Housing with pre-installed Air-Loc gasket	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See page 2 for max. trim rating)
IC23 W	6" Incandescent No Plate New Construction IC Housing with push-in electrical connectors for fast, secure installation	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See page 2 for max. trim rating)
IC23 W G	6" Incandescent No Plate New Construction IC Housing with push-in electrical connectors and pre-installed Air-Loc gasket	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See page 2 for max. trim rating)

Housing and trim can be ordered together or separate, but will always ship separately.

6" ECONOMY UNIVERSAL IC HOUSING

INCANDESCENT LAMPS

IC23 SERIES

TRIMS/LAMPS

	<u>'</u>	Catalog Number	Description	Max. Lamp Rating		
AIR-LOC		28 BWH ◆◆ 28 WWH ◆◆	Block Baffle, White Trim Ring White Baffle, White Trim Ring	60W A19, 65W BR30, † 75W PAR30/30L, 90W PAR38, 90W BR40		
AIR-LOC		29 CWH ◆◆ 29 WWH ◆◆	Clear Cone, White Trim Ring White Cone, White Trim Ring	60W A19, 65W BR30, † 75W PAR30/30L, 90W PAR38, 90W BR40		
		230 CBWH 230 CWWH	Clear with Black, Black Trim Ring Clear with White, White Trim Ring	40W A19		
		232 CWH 232 GWH 232 WWH 232 HZWH 232 WHZWH	Clear Alzak®, White Trim Ring Gold Alzak®, White Trim Ring White, White Trim Ring Haze, White Trim Ring Wheat Haze, White Trim Ring	60W A19		
		233 CWH	Clear Alzak®, White Trim Ring	40W A19		
AIR-LOC * *		244S BWH 244S WWH	Shallow Black Baffle, White Trim Ring Shallow White Baffle, White Trim Ring	75W PAR3OL, 65W BR3O, 60W PAR3O		
AIR-LOC * *		2475 CWH 2475 GWH 2475 BWH 2475 HZWH 2475 WHZWH	Shallow Clear Alzak® Cone, White Trim Ring Shallow Gold Alzak® Cone, White Trim Ring Shallow Black Alzak® Cone, White Trim Ring Shallow Haze Cone, White Trim Ring Shallow Wheat Haze Cone, White Trim Ring	75W PAR3OL, 65W BR3O, 75W PAR3O		
		250 WH 250 SC 250 ABZ	Open Frame, White Open Frame, Satin Chrome Open Frame, Classic Aged Bronze	65W BR30		
		226 BWH 226 WWH	Cylinder Spotlight, Black Baffle, White Trim Ring Cylinder Spotlight, White Baffle, White Trim Ring	60W PAR16		
		228 WH	Regressed Eyeball, White	50W PAR20/R20		
		229 WH 229 SC 229 ABZ 229 BL	Regressed Eyeball, White Regressed Eyeball, Satin Chrome Regressed Eyeball, Classic Aged Bronze Regressed Eyeball, Black	75W PAR3OL, 65W BR30		
		248 WWH	Regressed Eyeball, White Baffle, White Trim Ring	50W PAR20/R20		
		249 BWH 249 WWH	Regressed Eyeball, Black Baffle, White Trim Ring Regressed Eyeball, White Baffle, White Trim Ring	75W PAR3OL, 65W BR30		Trim Size: 75%" O.D. (except Cat. Nos. 228, 229, 241). Alzak is a registered trademark of Alcoa Corp. Note: In Canada when insulation is present, Type IC fixtures must be used.
**		264 BWH 264 WWH	Adjustable, Black Baffle, White Trim Ring Adjustable, White Baffle, White Trim Ring	50W PAR30	AIR-LOC	JUNO IC housings meet IECC Energy Code requirements per ASTM E283.
* *		267 CWH 267 GWH 267 BWH 267 HZWH 267 WHZWH	Clear Alzak® Cone, White Trim Ring Gold Alzak® Cone, White Trim Ring Black Alzak® Cone, Whit Trim Ring Haze Cone, White Trim Ring Wheat Haze Cone, White Trim Ring	50W PAR30		Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings. † Suitable for wet locations, ceiling mount only when used with 75W PAR30 or 90W PAR38
AIR-LOC		241 WH ◆ 241 PW ◆	Drop Opal w/Reflector, White Drop Opal w/Reflector, Plastic White	40W A19		OUTDOOR RATED LAMPS. • Wet location approved for covered coiling applications.
AIR-LOC		239 WH ◆	Frosted Lens, White	35W PAR3OL		ceiling applications. ** NOTE: TR6 Trim Ring compatible with 244S, 247S, 264, 267 trims.
		261 BWH 261 WWH	Wall Wash Scoop Trim, Black Baffle, White Trim Ring Wall Wash Scoop Trim, White Baffle, White Trim Ring	40W A19		Housing and trim can be ordered together or separate, but will always ship separately.