



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC44N IC44N 50W MR16 Lowtg HSG W/TFMR

Lithonia Lighting - Acuity

Catalog Number	IC44N
Manufacturer	Lithonia Lighting - Acuity
Description	The Energy-Efficient, Air-Loc Sealed Double Wall Construction Housing Does Not Require A Separate Air-Loc Gasket to Stop Infiltration and Exfiltration Of Air and Reduce Heating and Cooling Costs
Weight per unit	31.0 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round

Dimensions and Weight

Height	7.625
Length	16
Width	14

Descriptions

Construction	New Construction
Description	IC44N 50W MR16 LOVTG HSG W/TFMR
extra long description	LITH IC44N 4IN Low Voltage New Cons
Long Description	The energy-efficient, Air-Loc sealed double wall construction housing does not require a separate Air-Loc gasket to stop infiltration and exfiltration of air and reduce heating and cooling costs
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209017147
Manufacturers Part Number	IC44N
UPC	661209017147

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

Trade Size

aperture size	4 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight	6
Weight Per each	31

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	CSA,cUL