

SLOPE CEILING IC HOUSING

STANDARD SLOPE 2/12 to 6/12 PITCH (9° to 27°) INCANDESCENT LAMPS

IC926 SERIES

Project: Fixture Type: Location: Contact/Phone:

PRODUCT DESCRIPTION

Slope ceiling IC Housing "Air-Loc®" • Energy efficient, sealed inner housing • Double wall housing construction • Can be completely covered with insulation • When used with Air-Loc Gasket, stops infiltration and exfiltration of air, reducing heating and cooling costs.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected – see page 2.

Socket Medium base porcelain with nickel-plated copper screw shell

Adjustable to position lamp perpendicular to floor.

Trims Trim selection shown on page 2.

Labels UL listed for through-branch wiring, damp locations and IP

- Product thermally protected against improper use of lamps
 Union made
 UL Listed/CSA certified
 Trim No. 610 is wet location approved for covered ceiling applications.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance. Specifications subject to change without notice.

INSTALLATION

Real Nail® 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid - no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick onestep installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.


Junction Box Pre-wired junction box provided with (5) ½" and (1) 3/4" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates


• Knockouts equipped with pryout slots • W option is supplied with push-in electrical connectors for fast installation.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Access door for junction box accessibility • Inner housing is vertically adjustable to accommodate up to a 1" ceiling thickness • Designed to fit into 2 x 8 construction.

DIMENSIONS





Accessories **Catalog Number** Description ALG926 Air-Loc Gasket To order, specify catalog number

PRODUCT CODES

Catalog Numb	er	Input Voltage	Lamp Rating
IC926	6" Incandescent Slope Ceiling New Construction IC Housing	120V	A19/MR16/BR30/R30/PAR30/PAR30L/PAR38 (See page 2 for max. trim rating)
IC926 W	6" Incandescent Slope Ceiling New Construction IC Housing with push-in electrical connectors for fast, secure installation	120V	A19/MR16/BR30/R30/PAR30/PAR30L/PAR38 (See page 2 for max. trim rating)

Housing and trim can be ordered together or separate, but will always ship separately.

SLOPE CEILING IC HOUSING

STANDARD SLOPE 2/12 to 6/12 PITCH (9° to 27°) INCANDESCENT LAMPS

IC926 SERIES

TRIMS/LAMPS

	Catalog Number	Description	Max. Lamp Rating	
	610 BWH ◆ 610 WWH ◆	Lensed Shower Flat Diffuser Trim, Black Baffle, White Trim Ring Lensed Shower Flat Diffuser Trim, White Baffle, White Trim Ring	50W PAR30	
0	612 CWH 612 GWH 612 BWH 612 HZWH 612 HZSC 612 WWH 612 WHZWH 612 WHZWH	Clear Alzak® Cone, White Trim Ring Gold Alzak® Cone, White Trim Ring Black Alzak® Cone, White Trim Ring Haze Cone, White Trim Ring Haze Cone, Satin Chrome Trim Ring White Cone, White Trim Ring Wheat Haze Cone, White Trim Ring Wheat Haze Cone, Bronze Trim Ring	75W PAR30, 90W PAR38, 65W BR30	
	614 BWH 614 BSC 614 BBRZ 614 BBL 614 WWH	Standard Slope Downlight Black Baffle, White Trim Ring Standard Slope Downlight Black Baffle, Satin Chrome Trim Ring Standard Slope Downlight Black Baffle, Bronze Trim Ring Standard Slope Downlight Black Baffle, Black Trim Ring Standard Slope Downlight White Baffle, White Trim Ring	90W PAR38	Trim Size: 75%" O.D. (except Cat. Nos. 612 and 614 - 73%" O.D.). Note: In Canada when insulation is present, Type IC fixtures must be used.
	616 BWH 616 WWH	Cylinder Spotlight, Black Baffle, White Trim Ring Cylinder Spotlight, White Baffle, White Trim Ring	60W PAR16	◆ UL Listed for use in wet location.
	617 WWH	Cylinder Spotlight, White Baffle, White Trim Ring	35W MR16 supplied with magnetic transformer	Housing and trim can be ordered together or separate, but will always ship separately.
	619 BWH ¹ 619 WWH ¹	Eyeball, Black Baffle, White Trim Ring Eyeball, White Baffle, White Trim Ring	85W BR30	Notes: 1 Requires the C29 Adapter.