



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5617 Andrews Hwy  
79762-0000, TX Odessa  
Phone: 432-366-0008  
Fax: 432-366-6045



## IC928 IC928 HSNG Sloped Ceiling Ic

*Lithonia Lighting - Acuity*

Catalog Number	IC928
Manufacturer	Lithonia Lighting - Acuity
Description	IC928 Downlight Is An Ic-Rated, Double Wall Construction Housing For Use In 7/12- to 12/12-Pitch Slopes, 30- to 45-Degrees, Can Be Completely Covered With Insulation.
Weight per unit	18.0 (lbs/each)
Product Category	Incandescent Recessed Architec

### Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120

### Material, Color, and Finish

Color	Unfinished
-------	------------

### Dimensions and Weight

Height	7.625
Length	14
Width	16

### Descriptions

Construction	New Construction
Description	IC928 HSNG SLOPED CEILING IC
extra long description	LITH IC928 6IN Incandescent Super S
Long Description	IC928 downlight is an IC-rated, double wall construction housing for use in 7/12- to 12/12-pitch slopes, 30- to 45-degrees, can be completely covered with insulation.
Product Type	Housing

### Manufacturer Information

Brand	JUNO
GTIN	00661209000965
Manufacturers Part Number	IC928
UPC	661209000965

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5617 Andrews Hwy  
79762-0000, TX Odessa  
Phone: 432-366-0008  
Fax: 432-366-6045

## Trade Size

aperture size ..... 6 in

## Packaging

Carton ..... 1

Package ..... 4

Weight ..... 4

Weight Per each ..... 18

## Uses, Certifications, and Standards

Application ..... Education, Government, Healthcare, Hospitality, House of  
Worship, Offices & Banks, Residential, Retail

environmental conditions ..... Indoor

Mounting ..... Recessed

standard ..... CSA, UL