



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192



IC928W Super Slope Ic HSG Wego *Lithonia Lighting - Acuity*

Catalog Number	IC928W
Manufacturer	Lithonia Lighting - Acuity
Description	This Slope Ceiling Ic Housing Is Energy Efficient. When Used With Air-Loc Gasket, It Stops Infiltration and Exfiltration Of Air. This Reduces Heating and Cooling Costs.
Weight per unit	4.5 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	7
Length	18.5
Width	13.5

Descriptions

Construction	New Construction
Description	SUPER SLOPE IC HSG WEGO
extra long description	LITH IC928 W 6IN Incandescent Super
Long Description	This Slope ceiling IC Housing is energy efficient. When used with Air-Loc Gasket, it stops infiltration and exfiltration of air. This reduces heating and cooling costs.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209107817
Manufacturers Part Number	IC928 W
UPC	661209107817

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192

Packaging

Carton	1
Weight	4
Weight Per each	4.47

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA, UL