



SmartMate

SMARTMATE ICF2S26H1LDK

Offering maximum versatility, the Philips Advance family of SmartMate ballasts for 4-pin compact fluorescent lamps drive a broad range of quad and triple-tube, circline, 2D, and long twin-tube lamps. SmartMate ballasts' energy efficient design, compact and lightweight housing, and user-friendly features make these ballasts an ideal choice for fixture manufacturers, retrofitters, and MRO replacement.

Product data

General Information		Wir
Lamp Type	CFQ26W/G24Q	Cold
Number of Lamps	1/2 piece/unit	Cold
Ballast Type	Electronic Fluorescent	Wire
Base Model	ICF2S26H1LD	Lam
Suitable For Outdoor Use	Yes	Wire
Automatic Restart	Yes	Wire
		Wire
Operating and Electrical		Ren
Input Voltage	120 to 277 V	Tan
Input Frequency	50 to 60 Hz	Thro
Total Harmonic Distortion USA	10 %	Max
Ignition Method	Programmed Start	Max
Crestfactor (Nom)	1.5	Max
Ignition Time (Nom)	1.5 s	Con
Ballast Factor (Nom)	1	
Power Factor (Nom)	0.98	Ten
Input Current (Max)	0.43 A	T-Ca
Input Current (Min)	0.19 A	
Input Power (Nom)	51-51 W	Med
Rated Lamp Power	26 W	Hou
		Hou


Wiring	
Color Input Terminals	Black and White
Color Output Terminals	RED, YEL & BLU
Wire Striplength	0.375 mm
Lamp Connection	Series
Wire Length by Color	No wires
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	1-L = 15' / 2-L = 6'
Max Ballast-Lamp Distance Tandem Wiring	2-L: Red = 6'
Max Ballast-Lamp Distance Through Wiring	2-L: Red = 6'
Connector Type	Poke-In
Temperature	
T-Case Maximum (Nom)	75 °C
Mechanical and Housing	
Housing Material	Metal/Plastic
Housing	H1

SmartMate

Housing Dimensions	4.98" x 2.4" x 0.98"			
Approval and Application				
EMC Immunity Standard	FCC Non-Consumer			
Approval Marks	CSA certificate UL certificate CEC Listing NO			
	certificate RoHS Compliant			
Hum And Noise Level	A			
UL Recognized	No			
Product Data				
Order product name	SMARTMATE ICF2S26H1LDK			

EAN/UPC - Product	781087117781
Order code	913700500831
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700500831
Net Weight (Piece)	0.250 kg

Dimensional drawing



Product	A1	A2	A3	B1	C1
SMARTMATE ICF2S26H1LDK	4.60 in	4.20 in	2.00 in	2.40 in	0.98 in





© 2017 Philips Lighting Holding B.V. All rights reserved. Philips Lighting reserves the right to make changes in specifications and/or to discontinue any product at any timewithout notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.lighting.philips.com 2017, November 6 - data subject to change