



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICF2S42M2LDK 2-42W Comp 120-277V Plug In CFL Elec Bal

Advance By Signify

Catalog Number	ICF2S42M2LDK
Manufacturer	Advance By Signify
Description	Ballast, Programmed, 42 W, 277 V Ac, 0.78 A, CFTR42W/GX24Q Shape, Non Dimmable, 2 Lamps, 4.55 In Length, 3 In Width, 1.29 In Height, 0.97 Ballast Factor, 0.98 Power Factor, 50 to 60 HZ, Metal Housing Material, 10 % Total Harmonic Distortion, 5 Yr Warranty, 0.404 KG/Ea
Weight per unit	0.9200 (lbs/each)
Product Category	Electronic Compact Fluorescent

Features

Ballast Type	Electronic Fluorescent
Lamp Type	CFL
Wattage	42

Descriptions

Description	2-42W COMP 120-277V PLUG IN CFL ELEC BAL
extra long description	ADV 136977 ELE BAL (2) 42W CFL (4-P

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087117798
Manufacturers Part Number	136977
UPC	781087117798

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
----------------------	--------------------

Packaging

Carton	1
Package	12
Weight Per each	0.92

Uses, Certifications, and Standards

standard	CSA certificate;UL certificate;CEC Listing;NOM certificate;RoHS Compliant
----------	---------------------------------------------------------------------------