



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICN4S5490C2LSG35 F54T5HO 120-277V W/Leads

Advance By Signify

Catalog Number	ICN4S5490C2LSG35
Manufacturer	Advance By Signify
Description	No Matter What The Conditions Require, Operating At A Variety Of Line Voltages Between 120V to 480V, Whether Located In High Ambient Temperature Environments (Requiring A 90° C Rating) or Not, Our Family Of Philips Advance Centium Ballasts Are Ideal For A Wide Variety Of Applications.
Weight per unit	2.7 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	2.00-0.86
ANSI Code	N/A
Ballast Factor	1
dimmable	Non Dimmable
Lamp Type	Fluorescent
Minimum Starting Temperature	-20
Number of Lamps	4
Power Factor	0.98
start type	Programmed
total harmonic distortion	<=10
Voltage Rating	120-277
Wattage	240-234

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Height	4.65
Length	6.57
Width	6.69

Descriptions

extra long description	ADV 119404 ELE BALLAST (4) F54T5HO
Long Description	No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.
Product Type	Ele Ballast (4) F54T5HO 120-277V
Special Features	IntelliVolt 120-277V, Series Lamp Operation



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087047835
Manufacturers Part Number	ICN4S5490C2LSG35M
UPC	781087047835

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	ELECTRONIC

Packaging

Carton	1
Package	6
Weight Per each	2.68

Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	50to60
Mounting	16.34
standard	CSA certificate;UL certificate;CEC Listing;NOM certificate;RoHS Compliant