JUNO

Project:	
Fixture Type:	
Location:	
Contact/Phone:	

PRODUCT DESCRIPTION

ICTC Housing designed for use in insulated or non-insulated areas. Refer to lamp data for correct lamp wattage.

PRODUCT SPECIFICATIONS

Lamp IC - One 25W A19 lamp • TC - One 40W A19 lamp.

Socket Medium base porcelain with nickel-plated copper screw shell.

Trims Available in white baked enamel on steel • Fastens to housing with two torsion springs.

Labels UL listed for damp locations and IP • Product thermally protected against improper use of lamps • Union made • UL Listed/CSA certified.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Specifications subject to change without notice.

INSTALLATION

Real Nail 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail* 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edgemounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

Junction Box Pre-wired junction compartment provided with (3) ½" knockouts, and ground wire, UL Listed, C-UL/CSA certified for No. 12 AWG daisy chain circuit connectors suitable for 90° C permitted in junction box • Junction compartment provided with removable access plate • Knockouts equipped with pryout slots.

Housing TC housing, 22-gauge white painted steel • $8\,\%''$ L x $3\,\%''$ H x $3\,\%''$ D.

ORDERING INFORMATION: Housing and trim can be ordered together or separate, but will always ship separately.

Example (Trim): 104 WH		Example (Together): ICTC113 104 WH
Trims	Trim Finish	
104 Diffuse Glass Lens Step Light Trim	WH White	
840 Angled Louvers Step Light Trim		
	Trims 104 Diffuse Glass Lens Step Light Trim 840 Angled Louvers Step Light Trim	Trims Trim Finish 104 Diffuse Glass Lens Step Light Trim 840 Angled Louvers Step Light Trim

Trim Size: 9 $\%_6$ " L x 4 %" H Lamp Rating: 7W or 9W Twin Tube CFL.




G5.6.2

INCANDESCENT LOUVERED NIGHT LIGHT

INCANDESCENT LAMP

ICTC113

DIMENSIONS



8 3/4" X 3 3/4" WALL CUTOUT