## iDevices Wall Switch

# HUBBELL

#### **Features**

- Customizable LED
- Compatible with most standard light bulbs
- Wall Switch uses rocker for on/off
- Dimmer Switch uses rocker for adjustable dimming
- · High/low trim setting to prevent bulb flicker
- Works with any standard rocker faceplate
- Patent pending pull-out scroll for easy setup



### **Ordering Information**

DescriptionUPC NumberCatalog NumberThis Wi-Fi enabled smart switch852931005865IDEV0008HW

This Wi-Fi enabled smart switch allows for single pole, 3- and 4-way functionality, providing unparalleled flexibility anywhere in your home.

## **Specifications**

Horsepower - Maximum 1HP @ 120 & 277VAC

Lamp Type Tungsten: 960W @ 120VAC, 8A, Tungsten: 1800W @ 277VAC

Number Of Poles

Frequency Rating 50/60 Hz
Output Voltage 120-277 VAC

