

## Twist-Lock® Devices

### 20A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding

#### Isolated Ground Receptacle

#### Features

- Insulation barrier construction isolates ground contact from mounting strap
- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- High-impact, abuse-resistant nylon face
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

#### Ordering Information

Description	Device Color	UPC	Catalog Number
Isolated ground, nylon	Orange	783585872469	IG2510

#### Listings

Listed to UL 498  
Fed.Spec. W-C-596  
Certified to CSA C22.2 No.42

#### Specifications

Face	Nylon
Base	RTP
Contacts	Brass
Terminal Screws	#10 - 32 Brass
Mounting Strap	Brass

#### Performance

##### Electrical

Current Interrupting Certified for current interrupting at full rated current  
Dielectric Voltage Withstands 2,000V minimum

##### Mechanical

Flammability V2 or better per UL94/CSA 22.2 No.0.17  
Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire.  
Terminal Identification Terminals identified in accordance with UL 498


##### Environmental

Moisture Resistance IP20 Suitability  
Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

# HUBBELL



20A 3ØV  
120/208V AC  
NEMA L21-20R  
UL/CSA  
2 HP



#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

#### Accessories

Plug	HBL2511
Wallplate or Weatherproof Cover	1.60" Opening

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

