



## ISOLATED GROUND HEAVY-DUTY SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, ORANGE

IG5362 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Orange



- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Orange  
Type: Receptacles  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Isolated ground,back,side wire  
Style: Duplex

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes

Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### **DIMENSIONS**

Depth (US): 0.922"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Federal Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

