

Eaton IG5362BK

Catalog Number: IG5362BK

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 20A, Industrial, Flush, 125V, Back and side, Black, Brass, High-impact nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	IG5362BK
	UPC
	032664735417

Product Length/Depth	Product Height
1.3 in	4.19 in

Product Width	Product Weight
0.84 in	0.001 lb

Warranty	Compliances
Refer to warranty document.	RoHS Compliant

Certifications

UL
NOM
Federal Specification Classification 6233
01

Product specifications

Device type

Receptacle

Color

Black

Face/body material

High-impact nylon face

Glass-filled nylon base

Wiring method

Back and side

Features

Isolated ground

Material

Nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Duplex receptacle

Device grade

Heavy-duty industrial specification grade

NEMA configuration

5-20R

Style type

Standard

Design type

Straight blade

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - IG5362BK](#)

[Arrow Hart extra heavy duty industrial grade isolated ground straight blade receptacles](#)

Number of wires

3

Receptacle type

Duplex

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)