

Eaton IG5362GY

Catalog Number: IG5362GY

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 20A, Industrial, Flush, 125V, Back and side, Gray, Brass, High-impact nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	IG5362GY
	UPC
	032664735424

Product Length/Depth	Product Height
1.3 in	4.19 in

Product Width	Product Weight
0.84 in	0.001 lb

Warranty	Compliances
Refer to warranty document.	RoHS Compliant

Certifications

- UL
- NOM
- Federal Specification Classification 6233 01

Product specifications

Device type

Receptacle

Color

Gray

Face/body material

Glass-filled nylon base

High-impact nylon face

Wiring method

Back and side

Features

Isolated ground

Material

Nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Duplex receptacle

Device grade

Heavy-duty industrial specification grade

NEMA configuration

5-20R

Style type

Standard

Design type

Straight blade

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - IG5362GY](#)

[Arrow Hart extra heavy duty industrial grade isolated ground straight blade receptacles](#)

Number of wires

3

Receptacle type

Duplex

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)