



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5362I Duplex Recp 20A Commer Isol GRD Iv

Pass & Seymour/Legrand

Catalog Number	IG5362I
Manufacturer	Pass & Seymour/Legrand
Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.1950 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Isolated Ground, Straight Blade
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.922

Descriptions

Description	DUPLEX RECP 20A COMMER ISOL GRD IV
extra long description	P&S IG5362I RECEP DUP 20A COMMER IS
Features	Single Piece Plated Steel Mounting Strap
Long Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Recep Dup 20A Commer Isol GRD Iv
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007045338
Manufacturers Part Number	IG5362-I
UPC	785007045338

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.195

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC