

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



## IG5362W Duplex Recp 20A Commer Isol GRD WH Pass & Seymour/Legrand

Catalog Number	IG5362W
Manufacturer	Pass & Seymour/Legrand
Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.1950 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

#### **Features**

20
Back and side wire
Withstands 2000V minimum
Indoor
Nylon
3
Isolated Ground, Straight Blade
2
125.0 V
125
NO
Electrical power is expressed in Amps and Volts.
14 - 10

#### Material, Color, and Finish

Finish Matte	
--------------	--

#### **Dimensions and Weight**

Height	3.281	
Width	.922	



# ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

_				•	
1	2	cri	nti	$\mathbf{a}$	nc
		(.I I	UU	w	112
		•	P -	_	

Description	DUPLEX RECP 20A COMMER ISOL GRD WH
extra long description	P&S IG5362W RECEP DUP 20A COMMER IS
Features	Single Piece Plated Steel Mounting Strap
Long Description	Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Recep Dup 20A Commer Isol GRD WH
Special Features	IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi

#### **Manufacturer Information**

Brand	Pass and Seymour	
GTIN	00785007045383	
Manufacturers Part Number	IG5362-W	
UPC	785007045383	

### **Taxonomies, Classifications, and Categories**

Category Description	Residential receptacles
Type	Outlet

#### **Trade Size**

Amperage	20.0
Amperage	∠0.0

#### **Packaging**

• •		
Carton	1	
Package	100	
Weight Per each		

#### Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42, FEDSPEC