

Eaton IHB16L{UNV1

Catalog Number: IHB16L/UNV1

Eaton Crouse-Hinds series IHB industrial high bay LED light fixture, Cool white, Non-dimmable driver, 250W-500W HID or 4-lamp T5HO, Glass lens, 16000 lumens, 116 lm/W, Aluminum, No mounting module, Wide, 100-277 Vac, 127-250 Vdc, 145W

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series IHB industrial IHB16L/UNV1 high bay LED light fixture	UPC
	662276506763
Product Length/Depth	Product Height
18.83 in	4.23 in
Product Width	Product Weight
13.36 in	17 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Lumens

16000

Lumens per watt

116

Color temperature

Cool white

Mounting Method

No mounting module

Optical distribution

Wide

Dimming

Non-dimmable driver

Voltage rating

100-277 Vac, 127-250 Vdc

Frequency rating

50/60 Hz

Material

Aluminum

Lens material

Glass

Wattage

145W

Equivalent luminaire

250W-500W HID or 4-lamp T5HO

Power factor

0.99

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Industrial High Bay LED brochure](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

[Crouse-Hinds series DLC approved lighting products](#)

Catalogs

[Crouse-Hinds series Industrial High Bay LED catalog page](#)

Certification reports

[Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures UL certification](#)

[Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures Canadian certification](#)

[Industrial High Bay LED Light Fixtures Canadian certification \(Luminaire Fittings\)](#)

[Industrial High Bay LED Light Fixtures UL certification \(Luminaire Fittings\)](#)

Installation instructions

[IF 1726 - Industrial High Bay LED Light Fixture](#)

Specifications and datasheets

[Eaton Specification Sheet - IHB16L/UNV1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia