



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 W. Esthner Avenue
67213-0000, KS Wichita
Phone: 316-854-0028
Fax: 316-854-0029



IPC1102 1/0 Ins Piercing Tap

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | IPC1102 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Type Ipc - Talon Insulation Piercing Connector For Conductor Range Main: 1/0-8 Awg, 50-6 MM SQ., Tap: 2-8 Awg, 35-6 MM SQ. |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|--------------------------|-------|
| Number of Mounting Holes | 1 |
| Voltage Rating | 600 V |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1/0 INS PIERCING TAP |
| extra long description | ABB IPC1102 TALON INSUL CONN 1/0-8 |
| Long Description | Type IPC - Talon Insulation Piercing Connector for Conductor Range Main: 1/0-8 AWG, 50-6 MM sq., Tap: 2-8 AWG, 35-6 MM sq. |
| Product Type | Talon Insul Conn 1/0-8 2-8 |
| Special Features | For copper-to-copper, copper-to-aluminum and aluminum-to-aluminum applications (insulated conductor only). Performs as splice or tab for non-tension applications up to 600 volts, depending on size of connector |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Blackburn Mechanical |
| GTIN | 00783786331109 |
| Manufacturers Part Number | IPC1102 |
| UPC | 783786331109 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------|
| Category Description | SPLIT BOLTS |
| Type | Insulated Conductor Connectors |

Packaging

| | |
|-----------------|------|
| Carton | 30 |
| Package | 180 |
| Weight Per each | 0.26 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 W. Esthner Avenue
67213-0000, KS Wichita
Phone: 316-854-0028
Fax: 316-854-0029

Uses, Certifications, and Standards

standard

UL E9809
