



WIRE ENTRY PORT
WIRE RANGE: #4 - #14 AWG
PRE-FILLED W/ OXIDE INHIBITOR

IPL4-3C SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPL4-3C	3	1.55
IPL4-4C	4	1.97
IPL4-5C	5	2.39
IPL4-6C	6	2.81
IPL4-8C	8	3.66
IPL4-10C	10	4.51
IPL4-12C	12	5.35
IPL4-14C	14	6.20

NOTES:

- CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
- COLD TEMPERATURE RATED TO -45°C.
- HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT.

CONTACT NSi FOR SALES @ 800.321.5847

		POLARIS SALES . CO . INC					
PROPRIETARY AND CONFIDENTIAL		11625 PROSPEROUS DRIVE ODESSA, FL 33556					
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.		TITLE: CLEAR INSULATED #4 CONNECTOR					
<table border="1"> <thead> <tr> <th>NAME</th> <th>DATE</th> </tr> </thead> <tbody> <tr> <td>T.MITCHELL</td> <td>11/2021</td> </tr> </tbody> </table>		NAME	DATE	T.MITCHELL	11/2021	DWG. NO. IPL4C	
NAME	DATE						
T.MITCHELL	11/2021						
MATERIAL: N/A		SCALE: N/A					
		SHEET: 1 OF 1					