



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPL44 #4-#14 4 Pole Polaris Connector Block

Nsi Industries

Catalog Number	IPL44
Manufacturer	Nsi Industries
Description	The Polaris IPL4-4 Multi-Tap Single Side Entry Connector Features 4 Ports Sized For 4-14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, Panel Boards, Duct
Weight per unit	0.1100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	4
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	4-14 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=1.970 - W=1.188 - H=1.375
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#4-#14 4 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPL4-4 POLARIS Ins Multi-Tap 4
Features	The Polaris IPL4-4 4-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 4-14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength plas
Long Description	The Polaris IPL4-4 Multi-Tap Single Side Entry Connector features 4 ports sized for 4-14 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, panel boards, duct
Product Type	Polaris Ins Multi-Tap 4 4 Port Sse
Special Features	(4) 4-14 AWG - Dual Rated

Manufacturer Information

Brand	NSi
GTIN	00662381910028
Manufacturers Part Number	IPL4-4
UPC	662381910028

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Single Sided Entry

Packaging

Carton	6
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C