


**CABLE ENTRY** PLUG CP250

## IPLD250-5 SHOWN


PART NUMBER	NO. OF PORTS	LENGTH
IPLD250-3	3	2.98
IPLD250-4	4	3.85
IPLD250-5	5	4.71
IPLD250-6	6	5.57
IPLD250-8	8	7.29
IPLD250-10	10	9.01
IPLD250-12	12	10.74
IPLD250-14	14	12.46



**WIRE ENTRY POINT** WIRE RANGE: 250MCM - #6AWG PRE-FILLED W/ OXIDE INHIBITOR

## NOTES:

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
- 4. COLD TEMPERATURE RATED TO -45 °C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT
- 6. UV RATED





5/16 INTERNAL HEX PRESSURE SCREW

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

INSULATED DUAL ENTRY

250 CONNECTOR DWG. NO. NAME DATE IPLD250-DRAWN BY S.PARRY 2/9/2012

SCALE: N/A SHEET: 1 OF 1 MATERIAL: N/A