


FOR DUAL ENTRY (INSERT IN OTHER SIDE)

## IPLD350-5 SHOWN

| NO.<br>OF<br>PORTS | LENGTH                               |
|--------------------|--------------------------------------|
| 3                  | 3.52                                 |
| 4                  | 4.57                                 |
| 5                  | 5.62                                 |
| 6                  | 6.67                                 |
| 8                  | 8.77                                 |
| 10                 | 10.87                                |
| 11                 | 11.92                                |
| 12                 | 12.97                                |
| 13                 | 14.02                                |
| 14                 | 15.07                                |
| 16                 | 17.17                                |
| 18                 | 19.27                                |
|                    | OF PORTS 3 4 5 6 8 10 11 12 13 14 16 |



WIRE ENTRY POINT WIRE RANGE: 350MCM - #10AWG PRE-FILLED W/ OXIDE INHIBITOR- CONTACT NSi FOR SALES @ 800.321.5847

5/16 INTERNAL HEX PRESSURE SCREW

## **NOTES:**

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
- 4. COLD TEMPERATURE RATED TO -45 °C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION, CHEMICAL AND UV RESISTANT.



TITLE:

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556

2.61

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF

INSULATED DUAL ENTRY 350 CONNECTOR

 NAME
 REVISED

 DRAWN BY
 L. HILL
 4/17/2024

DWG. NO. IPLD350-SERIES

MATERIAL: N/A SCALE: 1:2 SHEET: 1 OF 1