



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell
88101-0000, NM Clovis
Phone: 575-742-2504
Fax: 575-742-2508



IPLD6003 Insd M-CBL Conn BLCK

Nsi Industries

Catalog Number	IPLD6003
Manufacturer	Nsi Industries
Description	The Polaris IPLD600-3 Multi-Tap Dual-Sided Entry Connector Features 3 Ports Sized For 600 MCM - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays
Weight per unit	1.6 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	600 MCM-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=4.550 - W=2.960 - H=3.030
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell
88101-0000, NM Clovis
Phone: 575-742-2504
Fax: 575-742-2508

Descriptions

Description	INSD M-CBL CONN BLCK
extra long description	NSI IPLD600-3 600 Mcm - 6 Awg Polar
Features	: The Polaris IPLD600-3 3-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 600 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric s
Long Description	The Polaris IPLD600-3 Multi-Tap Dual-Sided Entry Connector features 3 ports sized for 600 MCM - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays
Product Type	600 MCM - 6 Awg Polaris Insulated Multi-Tap Conn 3 Port (Dua
Special Features	(3) 600 MCM-6 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381789501
Manufacturers Part Number	IPLD600-3
UPC	662381789501

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Double Sided Entry

Packaging

Carton	3
Weight Per each	1.55

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	75 C
standard	UL 486A/B