


LENGTH 2.96

TO TIGHTEN SCREW (REPLACE WHEN COMPLETE)

> REMOVABLE CAP FOR DUAL ENTRY (INSERT IN OTHER SIDE)-

IPLD600-5 SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPLD600-3	3	4.55
IPLD600-4	4	5.85
IPLD600-5	5	7.15
IPLD600-6	6	8.45
IPLD600-7	7	9.75
IPLD600-8	8	11.05
IPLD600-10	10	13.65
IPLD600-12	12	16.25





WIRE ENTRY POINT WIRE RANGE: 600KCMIL - #6AWG PRE-FILLED W/ OXIDE INHIBITOR-

CONTACT NSi FOR SALES @ 800.321.5847

5/16 INTERNAL HEX PRESSURE SCREW

NOTES:

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. DUAL RATED FOR 75°C COPPER AND/OR ALUMINUM CONDUCTOR.
- 4. COLD TEMPERATURE RATED TO -45 °C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION, CHEMICAL AND UV RESISTANT.

POLARIS SALES CO INC

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556

TITLE:

INSULATED DUAL ENTRY 600 CONNECTOR

 NAME
 DATE

 DRAWN BY
 S.PARRY
 6/2012

DWG. NO. IPLD600-

MATERIAL: N/A SCALE: N/A SHEET: 1 OF 1