




LENGTH -3.41

TO TIGHTEN SCREW (REPLACE WHEN COMPLETE)

> REMOVABLE CAP FOR DUAL ENTRY (INSERT IN OTHER SIDE)

## IPLD750-5 SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPLD750-3	3	4.95
IPLD750-4	4	6.38
IPLD750-5	5	7.80
IPLD750-6	6	9.23
IPLD750-7	7	10.65
IPLD750-8	8	12.08
IPLD750-10	10	14.93
IPLD750-12	12	17.78
IPLD750-14	14	20.63





**WIRE ENTRY POINT** WIRE RANGE: 750KCMIL - 1/0 PRE-FILLED W/ OXIDE INHIBITOR-

CONTACT NSi FOR SALES @ 800.321.5847

## NOTES:

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. DUAL RATED FOR 75°C COPPER AND/OR ALUMINUM CONDUCTOR. 4. COLD TEMPERATURE RATED TO -45°C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT

6. UV RATED



-3/8 INTERNAL HEX PRESSURE SCREW

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556 TITLE:

INSULATED DUAL ENTRY 750 CONNECTOR

DWG. NO. NAME DATE IPLD750-DRAWN BY S.PARRY 6/2012

SCALE: N/A SHEET: 1 OF 1 MATERIAL: N/A