







PART NUMBER		WIRE RANGE CLASS B,C,D	WIRE RANGE CLASS K,M,I	LENGTH
IPLG1-3	3	1 - 1/0 AWG	2 - 10 AWG	2.24
IPLG1-4	4	1 - 1/0 AWG	2 - 10 AWG	2.89
IPLG1-6	6	1 - 1/0 AWG	2 - 10 AWG	3.54

## **NOTES:**

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. RATED FOR 90°C COPPER CONDUCTOR.
- 4. COLD TEMPERATURE RATED TO -45°C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION, CHEMICAL AND UV RESISTANT.

## **CONTACT NSi FOR SALES @ 800.321.5847**

