



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Alcock St.
79065-0000, TX Pampa
Phone: 806-665-0433
Fax: 806-665-1002



IPLMD35012 350MCM-10AWG 12PRT 2SIDE Multi-Tap Conn

Nsi Industries

| | |
|------------------|--|
| Catalog Number | IPLMD35012 |
| Manufacturer | Nsi Industries |
| Description | The Polaris IPLMD350-12 Multi-Tap Mountable Dual-Sided Entry Connector Features 12 Ports Sized For 350 MCM - 6 Awg Wires. Mounting Holes On Either Side Of The Connector Allow For Direct Mounting to Troughs, Panels or Wireways With 1/4" Bolts. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Wi |
| Weight per unit | 2.6 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|---------------|
| Number of Conductors | 12 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 350 MCM-6 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|------------------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |
| Housing Material | Aluminum |

Dimensions and Weight

| | |
|------|------------------------------|
| Size | L=14.570 - W=2.410 - H=2.770 |
|------|------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Alcock St.
79065-0000, TX Pampa
Phone: 806-665-0433
Fax: 806-665-1002

Descriptions

| | |
|------------------------|--|
| Description | 350MCM-10AWG 12PRT 2SIDE MULTI-TAP CONN |
| extra long description | NSI IPLMD350-12 3/0-6 Awg Polaris |
| Features | The Polaris IPLMD350-12 12-Port Dual-Sided Mountable Connector provides the simplest solution for forming a secure connection between up to twelve conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. Mountable connectors feature 1/4" mounting |
| Long Description | The Polaris IPLMD350-12 Multi-Tap Mountable Dual-Sided Entry Connector features 12 ports sized for 350 MCM - 6 AWG wires. Mounting holes on either side of the connector allow for direct mounting to troughs, panels or wireways with 1/4" bolts. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, wi |
| Product Type | 3/0-6 Awg Polaris Insulated Multi-Tap Conn 12PORT (Dual Sid |
| Special Features | (12) 350 MCM-6 AWG - Dual Rated - With Mounting Holes |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381944108 |
| Manufacturers Part Number | IPLMD350-12 |
| UPC | 662381944108 |

Taxonomies, Classifications, and Categories

| | |
|------|--|
| Type | Double Sided Entry With Mounting Holes |
|------|--|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 2.58 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |