



SignPRO

SIGNPRO MAG ELE SIGN BAL (1-4)T12HO 10-40FT 120-277V

Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps. Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps.

Product data

General Information				
Lamp Type	T12/HO			
Number of Lamps	1-4 piece/unit			
Lamp Footage	10 - 40 FT			
Ballast Type	Electronic Fluorescent			
Base Model	ISB104014EI			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	120 to 277 V			
Input Frequency	50 to 60 Hz			
Max THD	10 %			
Starting Method	Instant Start			
Lamp Current Crest Factor (Nom)	1.7			
Ignition Time (Nom)	0.1 s			
Ballast Factor (Nom)	0.61			
Power Factor (Nom)	0.98			


Input Current (Operating) (Nom)	2.88 A		
Input Power (Nom)	337 W		
Rated Lamp Watts	110 W		
Wiring			
Wire Striplength	0.50/0.375 mm		
Lamp Connection	Parallel		
Wire Length by Color	See data sheet		
Wire Gauge (Nom)	18AWG mm		
Wire Type	Solid		
Remote Wiring Configuration Allowed	No		
Tandem Wiring Configuration Allowed	No		
Through Wiring Configuration Allowed	Yes		
Max Ballast-Lamp Distance Remote Wiring	No Remote		
Max Ballast-Lamp Distance Tandem Wiring	No Tandem		
Max Ballast-Lamp Distance Through Wiring	Any = 20'		

SignPRO

Mechanical and Housing			
Housing Material	Metal		
Housing	BL2		
Housing Dimensions	14.31" x 3.19" x 2.63"		
Approval and Application			
EMC Immunity Standard	FCC Non-Consumer		
Approbation Marks	CSA certificate UL certificate RoHS Compliant		
Sound Rating	A		
UL Recognized	No		

Product Data			
Order product name	SIGNPRO MAG ISB104014EI		
EAN/UPC - Product	781087135808		
Order code	ISB104014EI		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	1		
Material Nr. (12NC)	913701262501		
Net Weight (Piece)	4.523 kg		

Dimensional drawing



Product	A1	A2	B1	C1
SIGNPRO MAG ISB104014EI	14.31 in	13.75 in	3.19 in	2.63 in



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips Lighting reserves the right to make changes in specifications and/or to discontinue any product at any timewithout notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.lighting.philips.com 2016, February 1 - data subject to change