

REMOVALBE CAPS FOR -ACCESS TO 3/16 INTERNAL HEX PRESSURE SCREWS










2/0 - #14 AWG CONDUCTOR PORTS ROCKET USED FOR #1-#14 DISCARD ROCKET FOR 1/0-2/0

**TORQUE CHART** 

WIRE RANGE	TORQUE (IN-LBS)
#10-#14	35
#8	75
#6-2/0	120







**CONTACT NSI FOR SALES @ 800.321.5847** 

## NOTES:

- DI-ELECTRIC SILICONE FILM ON ROCKET AND CAP FOR EASY ASSY/DISASSY.
- 2. PRE-FILLED W/ OXIDE INHIBITOR.
- 3. SHIPPED IN SEALED BAG W/ INSTALL INSTRUCTIONS.



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556 **TITLE:** 

IIILE:

2/0-#14 STREET LIGHT CONN. TWO PORTS FROM ONE SIDE ONE PORT FROM OPPOSITE SIDE

ISPBO 2/0

NAME DATE DWG. NO.

RAWNBY S.PARRY 2/24/2022

MATERIAL: 6061-T6511 ALUMINUM | SCALE: 1:1 | SHEET: 1 OF 1