



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299



## ISPB3504 350MCM-12AWG 4PRT Ped Conn

*Nsi Industries*

Catalog Number	ISPB3504
Manufacturer	Nsi Industries
Description	The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector Features 4 Ports Sized For 350 MCM - 12 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrenc
Weight per unit	0.7300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Number of Conductors	4
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-12 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=4.800 - W=4.190 - H=3.060
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299

## Descriptions

Description	350MCM-12AWG 4PRT PED CONN
extra long description	NSI ISPB350-4 Polaris Edge DB Conne
Features	The Polaris ISPB350-4 4-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to four conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in
Long Description	The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector features 4 ports sized for 350 MCM - 12 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench
Product Type	Polaris Edge DB Connector 350-12 4 Port
Special Features	(4) 350 MCM-12 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381788962
Manufacturers Part Number	ISPB350-4
UPC	662381788962

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Submersible Pedestal Connectors

## Packaging

Carton	2
Weight Per each	0.73

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1