



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISPB3506 350MCM-12AWG 6PRT Ped Conn

Nsi Industries

Catalog Number	ISPB3506
Manufacturer	Nsi Industries
Description	The Polaris ISPB350-6 Multi-Tap Direct Burial Single-Sided Entry Connector Features 6 Ports Sized For 350 MCM - 12 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrenc
Weight per unit	1.1 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	6
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-12 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=7.180 - W=4.190 - H=3.060
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	350MCM-12AWG 6PRT PED CONN
extra long description	NSI ISPB350-6 Polaris Edge DB Conne
Features	The Polaris ISPB350-6 6-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to six conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in h
Long Description	The Polaris ISPB350-6 Multi-Tap Direct Burial Single-Sided Entry Connector features 6 ports sized for 350 MCM - 12 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench
Product Type	Polaris Edge DB Connector 350-12 6 Port
Special Features	(6) 350 MCM-12 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381788979
Manufacturers Part Number	ISPB350-6
UPC	662381788979

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Submersible Pedestal Connectors

Packaging

Carton	2
Weight Per each	1.08

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1