







## NOTES:

- 1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- 2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- 3. DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.

WIRE ENTRY POINT -WIRE RANGE: 600 KCMIL - #6 AWG

PRE-FILLED W/ OXIDE INHIBITOR

- 4. COLD TEMPERATURE RATED TO -45 °C.
- 5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT
- 6. UV RATED



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

TITLE:

INSULATED 600 SPLICE CONNECTOR

NAME DATE DWG. NO. ISR600

MATERIAL: N/A | SCALE: N/A | SHEET: 1 OF 1