

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 Cavitt Avenue 77801-0000, TX Bryan Phone: 979-779-6630 Fax: 979-779-6620



IT030C 3/0-6AWG 2PRT, Os Insltd Tap Conn Nsi Industries

Catalog Number	IT030C
Manufacturer	Nsi Industries
Description	The Polaris Ito-3/0C Multi-Tap Offset Dual-Side Entry Vision Tap Connector Features 2 Ports Sized For 3/0 - 6 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Inclu
Weight per unit	0.1900 (lbs/each)
Product Category	Large Terminals & Connectors
Features	
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	3/0-6 AWG
Wire Type	Class B & C
Material, Color, and Finish	
Color	Clear
Finish	Plastisol Insulated
Housing Material	Aluminum
Dimensions and Weight	
Size	L=1.840 - W=1.870 - H=1.870



Enclosure

standard

environmental conditions

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 Cavitt Avenue 77801-0000, TX Bryan Phone: 979-779-6630 Fax: 979-779-6620

Descriptions	
Description	3/0-6AWG 2PRT,OS INSLTD TAP CONN
extra long description	NSI ITO-3/0C POLARIS Vision Tap 2 P
Features	The Polaris ITO-3/0C 2-Port Offset Dual-Sided Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 3/0 - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal condu
Long Description	The Polaris ITO-3/0C Multi-Tap Offset Dual-Side Entry Vision Tap Connector features 2 ports sized for 3/0 - 6 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, inclu
Product Type	Polaris Vision Tap 2 Port 3/0 Os
Special Features	(2) 3/0-6 AWG - Dual Rated - Offset Ports
Manufacturer Information	
Brand	NSi
GTIN	00662381996541
Manufacturers Part Number	ITO-3/0C
UPC	662381996541
Taxonomies, Classifications, and Ca	tenories
Category Description	TERMINALS
Type	Offset Entry
•	
Availability Status	Inactive
	Illactive
Packaging	
Carton	6
Weight Per each	0.19
Uses, Certifications, and Standards Application	Wire Termination

Clear Plastisol

UL 486A/B

Dry Location Only