



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900  
77047-0000, TX Houston  
Phone: 281-412-7049  
Fax: 281-412-7314



## ITH750 750MCM-1/0AWG 2PRT BLK HD Multi-Tap Conn

*Nsi Industries*

Catalog Number	ITH750
Manufacturer	Nsi Industries
Description	The Polaris Ith-750 Multi-Tap Dual-Sided Entry Connector Features 2 Ports Sized For 750 MCM - 1/0 Awg Wires. The Heavy-Duty Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Each Port Has Two Pressure Screws to Ensure The Best Connection Possible In Demanding Applications. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additi
Weight per unit	1.8 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	750-250 MCM
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=3.480 - W=4.500 - H=3.500
------	-----------------------------



## Descriptions

Description	750MCM-1/0AWG 2PRT BLK HD MULTI-TAP CONN
extra long description	NSI ITH-750 POLARIS Ins HD 2 Port 7
Features	<p>The Polaris ITH-750 2-Port Dual-Sided Heavy-Duty Connector provides the simplest solution for forming a secure connection between two conductors in challenging applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 MCM - 1/0 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high</p>
Long Description	<p>The Polaris ITH-750 Multi-Tap Dual-Sided Entry Connector features 2 ports sized for 750 MCM - 1/0 AWG wires. The heavy-duty body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Each port has two pressure screws to ensure the best connection possible in demanding applications. Installs with a hex key and torque wrench, without any tape or additi</p>
Product Type	Polaris Ins HD 2 Port 750
Special Features	(2) 750-250 MCM - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381926401
Manufacturers Part Number	ITH-750
UPC	662381926401

## Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
Type	Multi Cable

## Packaging

Carton	3
Weight Per each	1.75

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B