



Mark 7 0-10V

MARK 7 0-10V ELE DIMMING BALLAST(3)F32T8 120-277V

The Mark 7 0–10V series of dimmable electronic ballasts offer maximum versatility by incorporating separate control leads for use with a wide array of controllers, including occupancy sensors, daylight harvesting controls, and building management systems from more than 40 manufacturers. When paired with linear fluorescent and 4-pin compact fluorescent lamps, these ballasts optimize the benefits of such popular sustainable lighting techniques as daylight harvesting, occupancy sensing, and load shedding to satisfy the need for an affordable, flexible and versatile controllable lighting solution.

Product data

General Information			
Lamp Type	F32T8		
Number of Lamps	3 piece/unit		
Ballast Type	Dimmable Fluorescent		
Base Model	IZT3PSP32SC		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical			
Input Voltage	120 to 277 V		
Input Frequency	50 to 60 Hz		
Total Harmonic Distortion USA	10 %		
Ignition Method	Programmed Start		
Crestfactor (Nom)	1.6		
Ignition Time (Nom)	1.5 s		
Ballast Factor (Max)	1.00		
Ballast Factor (Min)	0.03		
Power Factor (Nom)	0.99		


Input Current (Max)	0.79 A	
Input Current (Min)	0.33 A	
Input Current (Nom)	- A	
Input Power (Max)	94 W	
Input Power (Min)	16 W	
Rated Lamp Power	32 W	
Wiring		
Color Input Terminals	No terminals	
Color Output Terminals	No terminals	
Wire Striplength	0.50/0.375 mm	
Control Wire Gauge	18AWG	
Lamp Connection	Series	
Wire Length by Color	See Data Sheet	
Wire Gauge (Nom)	18AWG mm	
Wire Type	Solid	
Remote Wiring Configuration Allowed	No	
Tandem Wiring Configuration Allowed	No	

Mark 7 0-10V

No
No Remote
No Tandem
s No Through
No connector
70 °C
Metal
SC
9.5" x 1.7" x 1.18"

Approval Marks	UL certificate CEC Listing CEE Rated NEMA
	Premium RoHS Compliant CSA certificate
Hum And Noise Level	A
UL Recognized	No
Product Data	
Order product name	MARK 7 0-10V ELE DIMMING
	BALLAST(3)F32T8 120-277V
EAN/UPC - Product	781087135396
Order code	913701261701
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913701261701
Net Weight (Piece)	441.000 g

Dimensional drawing



Product	A1	A2	B1	C1
MARK 7 0-10V ELE DIMMING BALLAST(3)F32T8	9.50 in	8.90 in	1.70 in	1.18 in
120-277V				

ELE DIMMING BALLAST (3) F32T8 120-277V



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change