



Hybrid Pliers with Crimper, Fish Tape Puller and Wire Stripper



Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and terminals make this a must-have tool for your bag.

Specifications

| | | | |
|--------------------------------------|---|-----------------------------------|--|
| Type: | High Leverage Stripping Crimping Shearing Side-Cut Hybrid Plier | Application: | Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire |
| Special Features: | High-Leverage Design | Overall Length: | 8.981" (22.8 cm) |
| Overall Height: | 0.75" (2 cm) | Overall Width: | 2.25" (6 cm) |
| Material: | Chrome-Vanadium Steel | Nose Type: | Square |
| Jaw Length: | 2.04" (0 cm) | Jaw Width: | 1.154" (0 cm) |
| Jaw Thickness: | 0.6" (1.5 cm) | Jaw Capacity: | 1.5" (3.8 cm) |
| Cutting Knives: | Yes | Knife Length: | 0.8" (2 cm) |
| Cut Style: | Side Cut | Strips and Cuts AWG Solid: | 10-14 |
| Strips and Cuts AWG Stranded: | 12-16 | Screw Shearing: | 6-32, 8-32 |
| Joint Type: | Solid | Handle Color: | Gray/Black |
| Handle Finish: | Journeyman™ Dual Material | Handle Length: | 5" (13 cm) |
| Insulated: | No | Tether Capable: | No |
| Weight: | 10.9 oz (308 g) | | |