



PRODUCT CODE	PART NUMBER	NOMINAL SIZE		A		A1		B	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
077721	JBA10	1/2	16	0.840	21	0.605	15	1.210	31
077722	JBA15	3/4	21	1.050	27	0.800	20	1.400	36
077723	JBA20	1	27	1.310	33	1.000	25	1.580	40
077724	JBA25	1 1/4	35	1.655	42	1.355	34	1.975	50
077725	JBA30	1 1/2	41	1.900	48	1.560	40	2.350	60
077726	JBA35	2	53	2.370	60	2.050	52	2.845	72
077727	JBA40	2 1/2	64	2.865	73	2.450	62	3.375	86
077728*	JBA45	3	76	3.500	89	3.040	77	3.960	101
077729*	JBA50	3 1/2	91	4.000	101	3.480	88	4.490	114
077730*	JBA55	4	103	4.500	115	4.016	102	5.000	127

PRODUCT CODE	PART NUMBER	NOMINAL SIZE		L		L1	
		(in)	(mm)	(in)	(mm)	(in)	(mm)
077721	JBA10	1/2	16	0.900	23	1.050	27
077722	JBA15	3/4	21	1.000	25.3	1.150	29
077723	JBA20	1	27	0.890	23	1.060	27
077724	JBA25	1 1/4	35	1.125	29	1.325	34
077725	JBA30	1 1/2	41	1.100	30	1.370	35
077726	JBA35	2	53	1.255	32	1.560	40
077727	JBA35	2 1/2	64	1.843	47	2.156	55
077728*	JBA45	3	76	2.020	51	2.380	61
077729*	JBA50	3 1/2	91	1.975	50.2	2.300	58
077730*	JBA55	4	103	2.375	60	2.687	68

* Not UL Listed