

Eaton JGH3150FAG

Catalog Number: JGH3150FAG

Eaton Series G complete molded case circuit breaker, JG-frame, JG, Fixed thermal, adjustable magnetic trip, Three-pole, 150 A, 600 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, 25 kAIC at 600 Vac, Line and load, Metric, 50/60 Hz, 80% rated



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series G complete molded case circuit breaker	JGH3150FAG
	UPC
	782113526843
Product Length/Depth	Product Height
3.57 in	7 in
Product Width	Product Weight
4.13 in	6 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	IEC Rated
	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Type

Complete breaker

Amperage Rating

150 A

Voltage rating

600 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

JG

Circuit breaker frame type

Complete breaker

Rating

80% rated

Series

Series G

Terminals

Line and load

Frame

JG

Frequency rating

50/60 Hz

Mounting hardware

Metric

Interrupt rating

100 kAIC at 240 Vac

65 kAIC at 480 Vac

25 kAIC at 600 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[High performance operating handles for Series G circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Series G MCCB quick selector](#)

[StrandAble terminals product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Motor protection circuit breakers product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Multi-wire lugs product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Breaker service centers](#)

[J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[AB DE-ION CIRCUIT BREAKER TYPE JG BRKR JG CURR LIMITER 3 POLE OUTLINE](#)

[JG-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Installation Instructions for Series G J-Frame Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - JGH3150FAG](#)

[MOEM MCCB product selection guide](#)

[Series G, J-frame Time Current Curve](#)

[NG and ND-Frame molded case circuit breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)