

Eaton JGH3250FAG

Catalog Number: JGH3250FAG

Eaton Series G complete molded case circuit breaker, JG Frame, 250 A, Three-pole, 600V, 100 kAIC at 240V, 70 kAIC at 415V, 65 kAIC at 480V, 25 kAIC at 600V, Line/load standard w/ metric mounting hardware, Fixed thermal, adj. magnetic



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series G complete molded case circuit breaker	JGH3250FAG
	UPC
	782113526874
Product Length/Depth	Product Height
3.57 in	4.13 in
Product Width	Product Weight
4.13 in	6 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	IEC Rated
	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

Type

Complete breaker

Amperage Rating

250 A

Voltage rating

600 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

JG

Circuit breaker frame type

Complete breaker

Rating

80% rated

Series

Series G

Terminals

Line and load

Frame

JG

Frequency rating

50 to 60 Hz

Mounting hardware

Metric

Interrupt rating

65 kAIC at 480 Vac

25 kAIC at 600 Vac

100 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Series G MCCB quick selector](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Circuit breaker motor operators product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[StrandAble terminals product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Breaker service centers](#)

[J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[AB DE-ION CIRCUIT BREAKER TYPE JG BRKR JG CURR LIMITER 3 POLE OUTLINE](#)

[JG-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Installation Instructions for Series G J-Frame Circuit Breakers](#)

Specifications and datasheets

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - JGH3250FAG](#)

[MOEM MCCB product selection guide](#)

[Series G, J-frame Time Current Curve](#)

Warranty guides



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)