



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JPL1509T 7 1/2HP 3450RPM 1PH 60HZ 213JP 3729L Open

Baldor/Abb Motors & Mechanical

Catalog Number	JPL1509T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Electric Motors, Pump, Single Phase, Close Coupled, Open Drip Proof, Horsepower: 7 1/2, RPM: 3450, Frame Size: 213JP, Voltage Rating: 208-230 Vac, Rotation: Counter Clockwise, Bearings: Ball, Service Factor: 1.15, Enclosure Type: Open Dripproof, Thermal P
Weight per unit	121.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	213 Im
horsepower	7.5 WO
Insulation Class	F
Phase	1 PH
Power Factor	0.82 in
Service Factor	1.15 lb
Speed Rating	3,450 rpm
Voltage Rating	230 VAC

Descriptions

Description	7 1/2HP 3450RPM 1PH 60HZ 213JP 3729L OPEN
extra long description	BALDOR JPL1509T 7.5HP,3450RPM,1PH,6
Long Description	Electric Motors, Pump, Single Phase, Close Coupled, Open Drip Proof, Horsepower: 7 1/2, RPM: 3450, Frame Size: 213JP, Voltage Rating: 208-230 VAC, Rotation: Counter Clockwise, Bearings: Ball, Service Factor: 1.15, Enclosure Type: Open Dripproof, Thermal P
Product Type	7.5HP, 3450RPM, 1PH, 60HZ, 213JP, 3729L, Open
Special Features	7.5HP,3450RPM,1PH,60HZ,213JP,3729L,OPEN

Manufacturer Information

Brand	BALDOR
GTIN	00781568114735
Manufacturers Part Number	JPL1509T
UPC	781568114735

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	121

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	OPEN
Frequency Rating	60 Hz
Mounting	F1