



## K2A29U, AL Universal Terminal, 2 Conductor, 1-Hole, #6 AWG Str-250 kcmil, 3/8" Stud, 2 Screws, Al/Cu Rated

By Burndy  
Catalog # [K2A29U](#)



Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-250 kcmil, 3/8" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

### Application

For Aluminum And Copper Conductors

### General

Connector Type	Parallel Set-Screw
EU RoHS Indicator	No
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque Recommended in-lb	275 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600108
UPC 12 Digit	7818106001088

### Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.50 in
Dimension - Height fraction	1.2 in
Dimension - Height inch	1.20 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in
Dimension - N inch	0.5 in
Dimension - Pad Width inch	1.66 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	3/8 in
Dimension - Width fraction	1-33/50 in
Dimension - Width inch	1.66 in
Dimension - Width mm	42 mm

### Electrical Ratings

Rating - Minimum Voltage 600

### Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	6 Str.- 250 Kcmil
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	6 Str.- 250 Kcmil
Conductor Size	6 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li></ul>
Number Of Conductors	2

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	144
Minimum Pack Quantity	6

### Product Assets

[3D Models - K2A29U\\_MODEL-STEP](#)  
[3D Models - K2A29U\\_MODEL-IGES](#)  
[3D Models - K2A29U\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - se210997](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-K2A29U-SPEC-EN | REV 8/2023