



Landscape Lights
T&B Catalog Number:

K805BR-8
 04226900504
 Active

UPC Number:
Status:
Description:

13 in. Landscape Light with Power Outlet Installation Post - Bronze

Features

Copper-free aluminum construction provides increased corrosion resistance
Sturdy die-cast aluminum construction provides durability
Architectural bronze color blends into landscape and deck areas
Aluminum mounting tube cap houses and protects wire connection (ground installed fixtures)
PVC ground tube provides an innovative installation method saving costly labor and traditional installation materials (ground installed fixtures)
Wire connectors and ground wire enable safe, easy power connections
Fixtures use regular household voltage, 120V.
Easy to install, only three wire connections per fixture are required
No need to pour concrete, all connections are made above ground.

Application

Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.
Low-profile fixture design for where low ceiling height presents a light problem
To light cold storage facilities, walkways, bridges, tunnels and security locations.
Used with colored globes as warning, caution or directional lights.
Ground-level safety/security lighting to illuminate dark areas
Suitable for use in wet locations

General

Color	Bronze
Globe Material	Lime crystal glass
Fixture Material	Die-cast zinc alloy ZAMAK 3
Mounting Tube Material	Gray PVC, schedule 40

Packaging

T&B Order Multiple	8
Package in Units	8
T&B Sold in UOM	Each
T&B Weight Per UOM	119 lbs. per 100

Application Support

T&B Instruction Sheets	ta02997-tb2
Product Overview	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com