

KAPO1/0

by Burndy
Catalog ID: KAPO1/0

Prop65

Wire range: 1/0 Awg-350 Kcmil, Torque: 100 N lb, Voltage: 600 V.

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

AL9CU- UL Listed for use with fine strand conductor



Product Details

General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Sub Brand	Pin Adaptor
Type	#6 - 1/0 Mechanical Pin Adaptor; Off-Centered Pin
UPC	621945493353

Dimensions

Height	1.43 in
Length	2.01 in
Width	1.12 in

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)