



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KC22 10AWG/3AWG Serv Post *Burndy LLC*

Catalog Number	KC22
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Flat, 10-3 Awg (STR) / 10-2 Awg (Sol), 3/8" Stud; Nut Torque: 275 In-LBS, Stud Torque: 280 In-LBS
Weight per unit	0.1100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	LEADED BRONZE ALLOY
pallet quantity	14850

Descriptions

Description	10AWG/3AWG SERV POST
extra long description	BUR KC22 10-3 STR 15/32 POST 1 CO
Long Description	Mechanical Grounding Connector, Cable to Flat, 10-3 AWG (Str) / 10-2 AWG (Sol), 3/8" Stud; Nut Torque: 275 in-lbs, Stud Torque: 280 in-lbs
Product Type	Mechanical
Special Features	Stud length: 15/32 IN; Thread size: 3/8-16; Diameter: 5/8 IN; Nut Width: 3/4 IN

Manufacturer Information

Brand	Burndy Canada
GTIN	00781810254905
Manufacturers Part Number	KC22
sub brand	Burndy Canada
UPC	781810254905

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	KC Series Mechanical Grounding Connector

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	For Direct Burial Applications And Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar
standard	UL467