



KC34 500 Post Split Bolt

Burndy LLC

Catalog Number	KC34
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Flat, 3/0 Awg - 500 Kcmil, 3/4" Stud.
Weight per unit	1.3 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper Alloy, Cast
pallet quantity	1

Descriptions

Description	500 POST SPLIT BOLT
extra long description	BUR KC34 3/0-500 STR 1 POST 1 CON
Long Description	Mechanical Grounding Connector, Cable to Flat, 3/0 AWG - 500 kcmil, 3/4" Stud.
Product Type	Mechanical
Special Features	Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Cross Flats: 2, 1-5/8 IN, Dimension B: 1 IN, Height: 3-5/8 IN, Stud Size: 3/4-10

Manufacturer Information

Brand	BURNDY
GTIN	00781810256701
Manufacturers Part Number	KC34
UPC	781810256701

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KC and K2C Series

Packaging

Carton	1
Weight Per each	1.3099

Uses, Certifications, and Standards

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
standard	UL467