

# Specifications



## Eaton KLM-20

Eaton Bussmann series KLM fuse, 20 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, 50 kAIC at 600 Vdc, Melamine tube, Nickel-plated bronze endcap, 600 V, 600 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series KLM fuse
<b>CATALOG NUMBER</b>	KLM-20
<b>UPC</b>	051712695206
<b>PRODUCT LENGTH/DEPTH</b>	0.001 in
<b>PRODUCT HEIGHT</b>	0.001 in
<b>PRODUCT WIDTH</b>	0.001 in
<b>PRODUCT WEIGHT</b>	0.18 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked



Powering Business Worldwide

## Electrical rating

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	100 kAIC at 600 Vac 50 kAIC at 600 Vdc
<b>VOLTAGE RATING</b>	600 Vac, 600 Vdc

## General information

<b>CONNECTION</b>	Ferrule end x ferrule end
<b>FUSE INDICATOR</b>	Non-indicating
<b>SPECIAL FEATURES</b>	Non-indicating

## Physical details

<b>MATERIAL</b>	Nickel-plated bronze endcap Melamine tube
<b>PACKAGING TYPE</b>	Standard

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - KLM-20</a>
TECHNICAL DATA SHEETS	<a href="#">KLM-20~LIMITRON FAST ACTING FUSE</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Datasheet - FNQ-30</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.