



KSU17, Split Bolt Connector with Spacer, Tin Plated

By Burndy
Catalog # [KSU17](#)

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length.



Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	165 LBS/in
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810035009
UPC 12 Digit	7818100350099

Dimensions

Dimension - Cross Flats inch	.62 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	1.14
Dimension - Width inch	0.42 in
Dimension - Width mm	11 mm
Width	0.42 in

Conductor Related

Conductor - AAAC 5005 Run	30.58 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Str Run	8 (6-1)
Conductor - ACSR Str Run Range	8 AWG
Conductor - ACSR Str Tap	8 (6-1)
Conductor - ACSR Str Tap Range	8 AWG
Conductor - AL Str Run	8 AWG;6 AWG
Conductor - AL Str Run Range	12 STR. 6 SOL.
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	12 STR. 6 SOL.
Conductor - Copper Solid Run	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Run Range	12 AWG-6 AWG
Conductor - Copper Solid Tap	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Tap Range	12 AWG-6 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Run Range	12 STR. 6 SOL.
Conductor - Copper Str Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Tap Range	12 STR. 6 SOL.
Conductor - Galvanized Steel Str Size	5/32 (7) in
Conductor - Galvanized Steel Str Size Range	5/32 (7) in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • AL C Str-Run

- AAAC C 5005-Run
- AAAC C 6201-Run
- ACSR C Str-Run
- CU C Solid-Tap
- CU C Str-Tap
- AL C Str-Tap
- AAAC C 5005-Tap
- AAAC C 6201-Tap
- ACSR C Str-Tap
- GAL Steel C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29700

Product Assets

- [3D Models - KSU17_MODEL-PDF](#)
- [3D Models - KSU17_MODEL-IGES](#)
- [3D Models - KSU17_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..041343-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-KSU17-SPEC-EN | REV 8/2023